

ACUTEL, INC.

OWL AVIATION OXIMETER

Interface:

¼" headphone jack w/ 10" cord (to connect to pilot headphones)

¼" headphone plug w/ 10" cord (to connect to aircraft audio)

9-pin connector for oximeter sensor

Alerts:

Audible-

“Caution” for oxygen saturation 90% to 86%

“Warning” for oxygen saturation 85% and below

“Caution” for oximeter sensor disconnected (immediate) and/or finger removed from sensor (after 90 seconds)

“Caution” for low battery condition

Visual-

Red LED to indicate low battery

Controls:

On/Off slide switch

Pushbutton for manual SpO₂ check

Volume adjustment

Each order consists of:

1 OWL aviation alert oximeter

1 articulated finger clip oximeter sensor with 2 meter cable

2 "AA" alkaline batteries

1 Instruction sheet

Optional Accessories:

Reflectance sensor-- for use in headband